



YSD28R2R, Aluminum Sleeve with Solid Center Barrier

By Burndy
Catalog # [YSD28R2R](#)



AL compression sleeve with solid center barrier, Designed for commercial and heavy residential services, Color Code: Pink (Side A), Red (Side B).

General

Catalog Number	YSD28R2R
Color Code - Side A	Pink
Color Code - Side B	Red
Die Index	249;K-840
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810146002
UPC 12 Digit	7818101460022

Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

Conductor Related

Conductor - ACSR Str Size A	4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size B	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size B Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size A	4/0 AWG
Conductor - AL Str Size B	1 AWG, 2 AWG
Conductor - AL Str Size B Range	1 AWG-2 AWG
Conductor - Copper Str Size A	4 AWG
Conductor - Copper Str Size B	1 AWG, 2 AWG
Conductor - Copper Str Size B Range	1 AWG-2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7400

Product Assets

- [3D Models - YSD28R2R_MODEL-PDF](#)
- [3D Models - YSD28R2R_MODEL-STEP](#)
- [3D Models - YSD28R2R_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YSD_LineArt](#)
- [Sales Drawings - sd046623-02](#)
- [Specifications - YSD28R2R](#)



A Hubbell brand