


YSH3429 Compression H-Tap Connector

By Burndy
Catalog # YSH3429



Copper Compression Double H - Tap Connector, 1/0 AWG - 250 kcmil (Tap 1), 1-6 AWG (Tap 2), 8-14 AWG (Tap 3), 4/0 AWG - 500 kcmil (Run).

Application

For High Voltage (15 KV) Power Cables With Copper Conductors

General

Catalog Number	YSH3429
Color Code	Brown
Connector Type	H-Tap
Die Index	1104
EU RoHS Indicator	Yes
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	Taps
UPC	781810038406
UPC 12 Digit	7818100384066

Dimensions

Dimension - Height inch	2.23 in
Dimension - Length Overall inch	3.00 in
Dimension - Strip Length inch	1 1/2
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

Conductor Related

Conductor - Copper Flex G Run	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Flex G Run Range	4/0 AWG-500 kcmil
Conductor - Copper Flex G Tap	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Flex G Tap Range	1/0 AWG-250 kcmil
Conductor - Copper Flex H Run	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Flex H Run Range	4/0 AWG-500 kcmil
Conductor - Copper Flex H Tap	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Flex H Tap Range	1/0 AWG-250 kcmil
Conductor - Copper Str Run	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	4/0 AWG-500 kcmil
Conductor - Copper Str Tap	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	1/0 -250 kcmil

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1920

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Catalogs - BURNDY Master Catalog - Section C - Compression

Connections

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_YSH_LineArt

Sales Drawings - 20880601

Specifications - YSH3429



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YSH3429-SPEC-EN | REV 8/2024