



## YSM6C, Uninsulated Parallel Splice For 10,380 - 26,813 cmils

By Burndy  
Catalog # YSM6C



Copper Compression Parallel Splice, 10380-26813 Circular Mil,  
0.44" Splice Length, Short Barrel, Tin Plated.

### Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

### Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

### General

Catalog Number	YSM6C
Connector Type	Parallel Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Temperature Rating	90
Trade Name	HYLINK™
Type	YSM
UPC	781810805787
UPC 12 Digit	7818108057877

### Dimensions

Dimension - Length Overall inch	0.44 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Strip Length inch	1/2

### Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG
Conductor - Copper Solid Size Range	14 AWG-12 AWG
Conductor - Copper Str Size	14 AWG;12 AWG
Conductor - Copper Str Size Range	14 AWG-12 AWG
Conductor Size	10,380 - 26,813 cmils
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	200
Minimum Pack Quantity	200

### Product Assets

- [3D Models - YSM6C\\_MODEL-IGES](#)
- [3D Models - YSM6C\\_MODEL-STEP](#)
- [3D Models - YSM6C\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094200](#)



A Hubbell brand