



YSU25R25R, Heavy-Walled Aluminum Tube with Solid Barrier

By Burndy
Catalog # [YSU25R25R](#)



Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code: Yellow (Side A), Yellow (Side B).

Application

For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 and Compressed Conductors

General

Catalog Number	YSU25R25R
Color Code - Side A	Yellow
Color Code - Side B	Yellow
Die Index	243;BG or 5/8
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	LINKIT
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated, Center Stop
UPC	781810143988
UPC 12 Digit	7818101439888

Dimensions

Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - ACSR Str Size A	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	1/0 (6/1) Raven AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	1/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	29600

Product Assets

- [3D Models - YSU25R25R_MODEL-STEP](#)
- [3D Models - YSU25R25R_MODEL-PDF](#)
- [3D Models - YSU25R25R_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YSU_LineArt](#)
- [Sales Drawings - sd052025-04](#)
- [Specifications - YSU25R25R](#)



A Hubbell brand