



YGA2C2TC38 Compression Grounding Lug, #2 AWG Cu, 2-Hole, 3/8" Stud

By Burndy
Catalog # [YGA2C2TC38](#)



HYLUG™ Copper Compression Terminal for Grounding; 2-Hole; 3/8" Stud; Long Barrel; Accommodates: #2 AWG

Application

For Direct Burial In Earth Or Concrete, Grounding Applications

General

Catalog Number	YGA2C2TC38
Color Code	Brown
Connector Type	Terminal
Die Index	10
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminals
UPC	781810109649
UPC 12 Digit	7818101096499

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size inch	0.38 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.48 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	3/8

Conductor Related

Conductor - Copper Solid Size	2
Conductor - Copper Solid Size Range	2
Conductor - Copper Str Size	2 Sol./2 Str.
Conductor - Copper Str Size Range	2 Sol./2 Str.
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL467• UL 486A-486B
Standards - Industry Standards Met	UL467;UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YGA2N_LineArt](#)
[Sales Drawings - SD209500](#)
[Specifications - YGA2C2TC38](#)



A Hubbell brand