



YGA6C2NTN Compression Grounding Lug, #6 AWG Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Tin Plated

By Burndy
Catalog # [YGA6C2NTN](#)



HYLUG™ Copper Compression Terminal for Grounding; 2-Hole; 1/2" Stud; 1-3/4" Spacing; Long Barrel; Accommodates: #6 AWG; Tin Plated.

General

| | |
|--|----------------------|
| Catalog Number | YGA6C2NTN |
| Color Code | Blue |
| Connector Type | Terminal |
| Die Index | 7;374 |
| Material | Copper |
| Physical Attribute - Number of Crimps Required | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Terminals |
| UPC | 781810359235 |
| UPC 12 Digit | 7818103592355 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length fraction | 1 in |
| Dimension - B Length inch | 1.09 in |
| Dimension - Bolt Hole Size inch | 0.52 in |
| Dimension - Bolt Size inch | 0.50 in |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - Hole Size mm | 14 mm |
| Dimension - L Length Overall mm | 112 mm |
| Dimension - Length Overall inch | 4.40 in |
| Dimension - N inch | 0.62 in |
| Dimension - Outside Diameter inch | 0.29 in |
| Dimension - Pad Width inch | 0.83 in |
| Dimension - Strip Length inch | 1-3/16 |
| Dimension - Stud Size inch | 1/2 |
| Dimension - Width fraction | 2/5 in |
| Dimension - Width inch | 0.41 in |

Conductor Related

| | |
|-----------------------------------|---|
| Conductor - Copper Str Size | 6 AWG |
| Conductor - Copper Str Size Range | 6 AWG |
| Conductor Type | <ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size |

Certifications And Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 100 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 24000 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD082469](#)
[Specifications - YGA6C2NTN](#)



A Hubbell brand