



YGHR26C34 Figure 8 Compression Ground Rod Connector

By Burndy
Catalog # [YGHR26C34](#)

Copper Compression Connector, 2 AWG(Str)-2/0 AWG(Str),
3/4" Ground Rod.



Application

For Direct Burial In Earth Or Concrete

General

Catalog Number	YGHR26C34
Connector Type	Tap
Die Index	998;1012
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Precrimp Die	UPRECRIMP58
Prefilled Oxide Inhibitor	Y
Sub Brand	HYGROUND, HYTAIL
Trade Name	HYTAIL™
Type	Taps
UPC	781810220726
UPC 12 Digit	7818102207266

Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	3/4
Dimension - Height fraction	2-15/79 in
Dimension - Height inch	2.19 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	2 AWG - 2/0 AWG
Conductor - Rod Size	3/4 in
Conductor - Rod Size Range	3/4 in
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size A• Rod-Size B

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL467• IEEE 837
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	4640

Product Assets

[3D Models - YGHR26C34_MODEL-STEP](#)
[3D Models - YGHR26C34_MODEL-IGES](#)
[3D Models - YGHR26C34_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YGHR-C_LineArt](#)
[Sales Drawings - sd..088266-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YGHR26C34-SPEC-EN | REV 8/2024