

YGHR34C34TN Figure 8 Compression Ground Rod Connector

By Burndy
Catalog # [YGHR34C34TN](#)



HYTAIL™ Ground Rod Figure 8 Compression Tap Connector.

General

| | |
|--------------------------------|----------------------|
| Catalog Number | YGHR34C34TN |
| Connector Type | Tap |
| Die Index | 998;1012 |
| Material | Copper |
| Physical Attribute - Number of | 1 |
| Crimps Required | |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYTAIL™ |
| Type | Taps |
| UPC | 781810238516 |
| UPC 12 Digit | 7818102385166 |

Dimensions

| | |
|---------------------------------|------------|
| Dimension - B Length fraction | 22/25 in |
| Dimension - B Length inch | 0.88 in |
| Dimension - Ground Rod Size | 3/4 |
| Dimension - Height fraction | 2-11/25 in |
| Dimension - Height inch | 2.44 in |
| Dimension - L Length Overall mm | 22 mm |
| Dimension - Length Overall inch | 0.88 in |

Conductor Related

| | |
|-----------------------------------|---|
| Conductor - Copper Str Size | 300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil |
| Conductor - Copper Str Size Range | 300 kcmil - 500 kcmil |
| Conductor - Rod Size | 3/4 in |
| Conductor - Rod Size Range | 3/4 in |
| Conductor Type | <ul style="list-style-type: none"> • CU C Str-Size A • Rod-Size B |

Certifications And Compliance

| | |
|---|---|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | <ul style="list-style-type: none"> • UL467 • IEEE 837 |
| Standards - Industry Standards Met | UL467;IEEE 837 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 20 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 4640 |

Product Assets

- [3D Models - YGHR34C34TN_MODEL-IGES](#)
- [3D Models - YGHR34C34TN_MODEL-STEP](#)
- [3D Models - YGHR34C34TN_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd..088266-01](#)
- [Specifications - YGHR34C34TN](#)