




# YP25U25, Figure 3-shaped Aluminum Connector with adjustable spacer

By Burndy  
Catalog # YP25U25



Wide range, universal and reversible, Figure 3 shaped aluminum connector with adjustable overhanging spacer that separates conductors, Conductor Groove A Solid: 2/0, 3/0.

## Application

For Copper, Aluminum Or ACSR Conductors

## General

Die Index	D3
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	CABELOK CRIMPIT
Trade Name	CABELOK™ CRIMPIT™
Type	YP-U
UPC	781810130322
UPC 12 Digit	7818101303222

## Dimensions

Dimension - Height inch	1.70 in
Dimension - Length Overall inch	1.69 in
Dimension - Width inch	0.97 in

## Conductor Related

Conductor - ACSR Str Size A	1 (6/1) Robin AWG; 1/0 (6/1) Raven AWG
Conductor - ACSR Str Size A Range	1 (6/1) Robin AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	1 (6/1) Robin AWG; 1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B Range	1 (6/1) Robin AWG-1/0 (6/1) Raven AWG
Conductor - AL Str Size A	1 AWG; 1/0 AWG
Conductor - AL Str Size A Range	1 AWG-1/0 AWG
Conductor - AL Str Size B	1 AWG; 1/0 AWG
Conductor - AL Str Size B Range	1 AWG-1/0 AWG
Conductor - Copper Solid Size A	2/0 AWG; 3/0 AWG
Conductor - Copper Solid Size A Range	2/0 AWG-3/0 AWG
Conductor - Copper Solid Size B	2/0 AWG; 3/0 AWG
Conductor - Copper Solid Size B Range	2/0 AWG-3/0 AWG
Conductor - Copper Str Size A	1 AWG; 1/0 ; 2/0 AWG
Conductor - Copper Str Size A Range	1 AWG-2/0 AWG
Conductor - Copper Str Size B	1 AWG; 1/0 ; 2/0 AWG
Conductor - Copper Str Size B Range	1 AWG-2/0 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[3D Models - YP25U25\\_MODEL-IGES](#)  
[3D Models - YP25U25\\_MODEL-STEP](#)  
[3D Models - YP25U25\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Literature - YP25U25](#)



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YP25U25-SPEC-EN | REV 8/2023