



# 1PBS2, UV Rated Black Splicer/Reducer, 2 #14-2 kcmil

By Burndy  
Catalog # 1PBS2



UV Rated Black UNITAP™, 2, #14 - 2 Kcmil, 2.38 in L, 0.75 in W.

## Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

## General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Catalog Number	1PBS2
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	1/8
Installation Torque	45 in-lb
Recommended in-lb	
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of	2
Screws	
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194° F
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810329658
UPC 12 Digit	7818103296588

## Dimensions

Dimension - Height inch	1.22 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Screw Size inch	5/16
Dimension - Width fraction	3/4 in
Dimension - Width inch	0.75 in
Dimension - Width mm	19 mm

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - AL Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Size Range	14 AWG - 2 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	14 AWG - 2 AWG
Conductor Size	14-2 AWG
Conductor Type	AL C Str-Size CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct	No
Burial	
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_PBS\\_LineArt](#)
- [Sales Drawings - SD214514-03](#)



A Hubbell brand