


YSH2929 Compression H-Tap Connector

By Burndy
Catalog # [YSH2929](#)



Copper Split Compression Wye Tap Connector, 250-2 (4/0-2) (Tap), Provides maximum design and installation flexibility.

Application

For High Voltage (15 KV) Power Cables With Copper Conductors

General

| | |
|--|---------------|
| Color Code | Purple |
| Connector Type | H-Tap |
| Die Index | 654 |
| EU RoHS Indicator | Yes |
| Material | Copper |
| Physical Attribute - Number of Crimps Required | 2 |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | CRIMPIT |
| Trade Name | CRIMPIT™ |
| Type | Taps |
| UPC | 781810036969 |
| UPC 12 Digit | 7818100369699 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 1.85 in |
| Dimension - Length Overall inch | 3.00 in |
| Dimension - Strip Length inch | 1 1/2 |
| Dimension - Width inch | 0.90 in |
| Dimension - Width mm | 23 mm |

Conductor Related

| | |
|-------------------------------------|---|
| Conductor - Copper Flex G Run | 2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil |
| Conductor - Copper Flex G Run Range | 2 AWG-250 kcmil |
| Conductor - Copper Flex G Tap | 2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil |
| Conductor - Copper Flex G Tap Range | 2 AWG-250 kcmil |
| Conductor - Copper Flex H Run | 2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil |
| Conductor - Copper Flex H Run Range | 2 AWG-250 kcmil |
| Conductor - Copper Flex H Tap | 2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil |
| Conductor - Copper Flex H Tap Range | 2 AWG-250 kcmil |
| Conductor - Copper Str Run | 2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil |
| Conductor - Copper Str Run Range | 2 AWG-250 kcmil |
| Conductor - Copper Str Tap | 2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil |
| Conductor - Copper Str Tap Range | 2 AWG-250 kcmil |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 20 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 2880 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YSH2929-SPEC-EN | REV 5/2024