



# Compression Splice Reducer

By Burndy  
Catalog # [YSR284CFXLTKITC](#)

CU Splice Reducer, Barrel A 4/0 AWG, Barrel B 4 Flex G,H,I,K,M,DLO, 4 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Purple/Gray Color Code, 15/8 Die Index.



## Application

Wire Reducing Splice

## General

Color Code	Purple, Gray
Color Code - Side A	Purple
Color Code - Side B	Gray
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	15/8
Die Index - Element A	15
Die Index - Element B	8
Die Index Run Side	15
Die Index Tap Side	8
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810490655
UPC 12 Digit	7818104906555

## Dimensions

Dimension - B Length fraction	1-5/16 in
Dimension - B Length inch	1.30 in
Dimension - L Length Overall mm	68 mm
Dimension - Length BB inch	0.74 in
Dimension - Length Overall inch	2.69 in
Dimension - Strip Length inch	1.24 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Size B	4 AWG
Conductor - Copper Flex G Tap	4 AWG
Conductor - Copper Flex H Size B	4 AWG
Conductor - Copper Flex H Tap	4 AWG
Conductor - Copper Flex I Size B	4 AWG
Conductor - Copper Flex I Tap	4 AWG
Conductor - Copper Flex K Size B	4 AWG
Conductor - Copper Flex K Tap	4 AWG
Conductor - Copper Flex M Size B	4 AWG
Conductor - Copper Flex M Tap	4 AWG
Conductor - Copper Str Size	4/0 AWG-4 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG-4 AWG
Conductor Type	CODE/FLEX
Wire Size	4/0 AWG-4 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	1728

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SPLICE KIT trilingual](#)
- [Sales Drawings - 10021428](#)



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YSR284CFXLTCKITC-SPEC-EN | REV 5/2024