



## **YST2525, Compression T-Connector, 1/0 Str Cu, Standard Barrel, Tapered Ends**

By Burndy  
Catalog # [YST2525](#)

Cu compression T-Coupler, 1/0str(Run), 1/0str(Tap),  
Pink(Run&Tap), 12(Run&Tap) Index.



## Application

T-Connector

## General

Catalog Number	YST2525
Color Code	Pink
Color Code - Side A	Pink
Color Code - Side B	Pink
Connector Type	T-COUPLER
Die Index	12/12
Die Index Run Side	12
Die Index Tap Side	12
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYTEE
Temperature Rating	194
Trade Name	HYTEE™
Type	YST, Uninsulated T
UPC	781810001134
UPC 12 Digit	7818100011344

## Dimensions

Dimension - A Outside Diameter inch	0.51 in
Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - B Outside Diameter inch	0.51 in
Dimension - Height inch	1.91 in
Dimension - L Length Overall mm	97 mm
Dimension - Length BB inch	1.56 in
Dimension - Length Overall inch	3.81 in
Dimension - Width inch	1.56 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Run	1/0 AWG
Conductor - Copper Str Run Range	1/0 AWG
Conductor - Copper Str Tap	1/0 AWG
Conductor - Copper Str Tap Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG-1/0 AWG
Conductor Type	CODE

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	11600

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YST\\_LineArt](#)  
[Sales Drawings - 238867](#)  
[Specifications - YST2525](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YST2525-SPEC-EN | REV 8/2024