



**YST2626, Compression T-Connector,
2/0 Str Cu, Standard Barrel,
Tapered Ends**

By Burndy
Catalog # [YST2626](#)

Cu compression T-Coupler, 2/0str(Run), 2/0str(Tap),
Black(Run&Tap), 13(Run&Tap) Index.



Application

T-Connector

General

Catalog Number	YST2626
Color Code	Black
Color Code - Side A	Black
Color Code - Side B	Black
Connector Type	T-COUPLER
Die Index	13/13
Die Index Run Side	13
Die Index Tap Side	13
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYTEE
Temperature Rating	194
Trade Name	HYTEE™
Type	YST, Uninsulated T
UPC	781810500989
UPC 12 Digit	7818105009899

Dimensions

Dimension - A Outside Diameter inch	0.56 in
Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - B Outside Diameter inch	0.56 in
Dimension - Height inch	2.18 in
Dimension - L Length Overall mm	100 mm
Dimension - Length BB inch	1.67 in
Dimension - Length Overall inch	3.94 in
Dimension - Width inch	1.62 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Run	2/0 AWG
Conductor - Copper Str Run Range	2/0 AWG
Conductor - Copper Str Tap	2/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG-2/0 AWG
Conductor Type	CODE

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YST_LineArt](#)
[Sales Drawings - 2388608](#)
[Specifications - YST2626](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YST2626-SPEC-EN | REV 8/2024