



# YSU25R2R, Heavy-Walled Aluminum Tube with Solid Barrier

By Burndy  
Catalog # YSU25R2R



Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code: Yellow (Side A), Red (Side B).

## Application

Heavy-walled Aluminum tubing with solid barrier minimizes galvanic corrosion of conductors

## General

Color Code - Side A	Yellow
Color Code - Side B	Red
Construction Material - Main	Aluminum
Die Index	243;BG or 5/8
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	LINKIT
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated, Center Stop
UPC	781810143285
UPC 12 Digit	7818101432855

## Dimensions

Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2 in
Dimension - Outside Diameter inch	0.65 in

## Conductor Related

Conductor - ACSR Str Size A	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size B Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	2 AWG;1 AWG
Conductor - AL Str Size B Range	2 AWG-1 AWG
Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	1 AWG, 2 AWG, 3 AWG
Conductor - Copper Str Size B Range	1 AWG- 3 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	29600

## Product Assets

- [3D Models - YSU25R2R\\_MODEL-PDF](#)
- [3D Models - YSU25R2R\\_MODEL-STEP](#)
- [3D Models - YSU25R2R\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - sd052025-04](#)



A proud member of the Hubbell Family.

