

# AGSKIT2, Splice Kit, 8-2 AWG, Heavy Wall Heat Shrink Sleeve, Al/Cu Rated

By Burndy  
Catalog # [AGSKIT2](#)



Splice Kit, 8-2 AWG, w/ Heavy Wall Heat Shrink Sleeve, Al/Cu Rated.

## Features

- Dual Rated - Aluminum or Copper/Aluminum Combinations
- Installed with common installation tools
- Heavy wall heat shrink sleeve is lined with adhesive material providing a positive seal against moisture egress

## General

Application	For All Aluminum or Copper/Aluminum Combinations
Catalog Number	AGSKIT2
Connector Type	Splice/Heat Shrink Kit
EU RoHS Indicator	Yes
Hex Size	Slot
Insulation	Y
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	SPLICE KIT
Temperature Rating	194° F
Type	AGSKIT, Above Grade
UPC	781810175293
UPC 12 Digit	7818101752933

## Dimensions

Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Size Range	8 AWG-2 AWG
Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor Size	8-2 AWG
Conductor Type	AL C Str-Size CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_AGSKIT\\_LineArt](#)  
[Sales Drawings - SD..211383-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-AGSKIT2-SPEC-EN | REV 6/2024