

## CS3CI585001000J, Medium Voltage Cold Shrink Termination Kit, 5-8kV 3-Phase Conversion Series-Indoor, Sleeve w/o Boot for Jacketed Concentric Conductor

By Burndy

Catalog # [CS3CI585001000J](#)

The Type CS3CI58-J Series of 3 Phase Conversion Kits with Outdoor Sleeves without Boot for Jacketed Concentric Conductor. Conversion kits includes indoor cold shrinkable tube (unprinted), seal, cable tie, and installation guide. Conforms to IEEE-48-2009, Class 1 and ISO/IEC 17025 Standards. Test reports available upon request.

### Features

- Rip and Grip does not require heat gun or any installation tools
- Spiral rip cord design provides for easy installation with effortless unwinding providing for fast removal of the hold-out core, Rip cord is recyclable
- All kits supplied with indoor cold shrinkable tube (unprinted), seal, cable tie, and installation guide
- Quick, easy, cost effective installation utilizing one-piece terminator design
- Test reports available upon request
- L'agrippe-câble ne nécessite pas de pistolet thermique ni d'outils d'installation
- La conception en spirale de l'agrippe-câble permet une installation facile avec un déroulement sans effort permettant un retrait rapide du noyau de retenue, l'agrippe-câble est recyclable
- Tous les kits sont fournis avec une gaine thermorétractable intérieure (non imprimée), un joint, un serre-câble et un guide d'installation
- Installation rapide, facile et rentable grâce à la conception de l'agrippe-câble en une seule pièce
- Rapports d'essai disponibles sur demande



### General

Boot Type	NO
Catalog Number	CS3CI585001000J
Environmental Conditions	
Material	Caoutchouc de silicone
Pin Type	N/A
Series	UD-JC
Terminal Type	N/A
Type	
UPC	621945585010

### Electrical Ratings

Phase	3-Phase
Voltage Rating	5/8 kV

### Conductor Related

Conductor Range	500 - 1000 kcmil
-----------------	------------------

### Logistics

Carton Quantity	1
-----------------	---

### Product Assets

- [Brochures - Cold Shrink Medium Voltage Cable Terminations Brochure](#)
- [Catalog Page - BURNDY MVColdShrinkTerminationKits CS3CI-J CatCut](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50095782](#)
- [Specifications - CS3CI585001000J Specification Sheet French](#)



A Hubbell brand