



# FQN18F25X03D, Fully Insulated Nylon Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy  
Catalog # [FQN18F25X03D](#)

Brass Fully Insul Female Quick Disconnects, Funnel Entry, 18-22 AWG, 300 V, 0.90" L, 0.25" W, Nylon Insul, Red(Insul Color).



## Features

- Fully insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent for a firm grip

## General

Application	For quickly connecting or disconnecting a terminal
Catalog Number	FQN18F25X03D
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293010
UPC 12 Digit	7818102930100

## Dimensions

Dimension - Length Overall inch	0.90 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

## Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	600
Pallet Quantity	99999

## Product Assets

- [3D Models - FQN18F25X03D\\_MODEL-STEP](#)
- [3D Models - FQN18F25X03D\\_MODEL-IGES](#)
- [3D Models - FQN18F25X03D\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_FFQNF\\_LineArt](#)
- [Sales Drawings - 50094212](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-FQN18F25X03D-SPEC-EN | REV 6/2024