



KA29U, AL Set Screw Connector, 1-Hole, #6 AWG Str-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated

By Burndy
Catalog # [KA29U](#)

Aluminum Universal Terminal, 1 Hole, 6 AWG (Str)-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated, Tin Plated.



Features

Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

General

Application	For Aluminum And Copper Conductors
Catalog Number	KA29U
Connector Type	Terminal
EU RoHS Indicator	Yes
Installation Torque	275 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type Plated	Allen Y
Plating Type	Tin
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370155

Dimensions

Dimension - Bolt Hole Size inch	0.31 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.94 in
Dimension - Height fraction	1.14 in
Dimension - Height inch	1.14 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - N inch	0.47 in
Dimension - Pad Width inch	1.02 in
Dimension - Stud Size inch	5/16
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - AL Str Size	6;4;3;2;1;1/0;2/0;3/0;4/0;250
Conductor - AL Str Size Range	6-250
Conductor - Copper Str Size	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250
Conductor - Copper Str Size Range	6-250
Conductor - Nominal Diameter	0.184, 0.184, 0.206, 0.232, 0.232, 0.260, 0.260, 0.292, 0.320, 0.328, 0.360, 0.368, 0.390, 0.414, 0.438, 0.464, 0.492, 0.522, 0.528, 0.574, 0.600
Conductor Size	6 AWG-250 KCMIL
Conductor Type	AL C Str-Size CU C Str-Size CU C Solid-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved Yes

Certification - UL Listed Direct No

Burial

Industry Standard(s) UL 486A-486B

Standards - Industry Standards UL 486A-486B

Met

Standards - RoHS Compliance EX

Status

UL Listed Yes

Logistics

Carton Quantity 400

Product Assets

[3D Models - KA29U_MODEL-PDF](#)

[3D Models - KA29U_MODEL-IGES](#)

[3D Models - KA29U_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_KAU_Lineart](#)

[Sales Drawings - se210997](#)



A Hubbell brand