



KA36U, Aluminum Universal Terminal, 1 Hole, 2 AWG (Str)-600 kcmil, 3/8" Stud, 1 Screw, Al/Cu Rated, Tin Plated.

By Burndy
Catalog # [KA36U](#)



Aluminum Universal Terminal, 1 Hole, 2 AWG (Str)-600 kcmil, 3/8" Stud, 1 Screw, Al/Cu Rated, Tin Plated.

Features

Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

General

Application	For Aluminum And Copper Conductors
Catalog Number	KA36U
Connector Type	Terminal
EU RoHS Indicator	Yes
Installation Torque	550
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Sub Brand	UNIVERSAL TERM
Type	Bolted Lugs & Terminals
UPC	781810370254

Dimensions

Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.72 in
Dimension - Height inch	1.58 in
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in
Dimension - N inch	0.78 in
Dimension - Pad Width inch	1.52 in
Dimension - Stud Size inch	3/8
Dimension - Width fraction	1-1/2 in
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm

Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Size Range	2 AWG-600 kcmil
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil
Conductor - Copper Str Size Range	2 AWG-600 kcmil
Conductor Size	2 AWG-600 KCMIL
Conductor Type	AL C Str-Size CU C Str-Size CU C Solid-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved Yes

Certification - UL Listed Direct No

Burial

Industry Standard(s) UL 486A-486B

Standards - Industry Standards UL 486A-486B

Met

Standards - RoHS Compliance EX

Status

UL Listed Yes

Logistics

Carton Quantity 120

Product Assets

[3D Models - KA36U_MODEL-STEP](#)

[3D Models - KA36U_MODEL-IGES](#)

[3D Models - KA36U_MODEL-PDF](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_KAU_Lineart](#)

[Sales Drawings - se210997](#)



A Hubbell brand