



# BIBS75010, Single Sided Ten Conductor Clear Insulated Multi-Tap Connector

By Burndy  
Catalog # [BIBS75010](#)



MULTI-PORT Single-Sided Entry.

## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

## General

Catalog Number	BIBS75010
Connector Type	Multi Tap
Hex Key	3/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	10
Physical Attribute - Number of Screws	10
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	781810233108
UPC 12 Digit	7818102331088

## Dimensions

Dimension - Height inch	3.00 in
Dimension - L Length Overall mm	346 mm
Dimension - Length Overall inch	13.63 in
Dimension - Width inch	2.70 in
Dimension - Width mm	69 mm

## Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

## Conductor Related

Conductor - AL Str Size Range	2 AWG - 750 kcmil
Conductor - Copper Str Size Range	2 AWG - 750 kcmil
Conductor Size	2 AWG-750 KCMIL
Conductor Type	AL C Str-Size CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BIBS\\_Lineart](#)
- [Sales Drawings - sc210991-15](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-BIBS75010-SPEC-EN | REV 6/2024