



# PATRIOT 12-Ton Covered C-Head Battery Crimper, Hydraulic Self-Contained, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag

By Burndy  
Catalog # [PAT750CLIPB](#)



PATRIOT® 12-Ton Covered C-Head Battery Crimper, Hydraulic Self-Contained, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag.

## Application

Crimping

## General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUNDR® Compression Grounding
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT750CLIPB
Container Type	Nylon Pro Bag
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561441
UPC 12 Digit	621945561441

## Dimensions

Dimensions	15.75 in x 3.50 in x 13.50 in
Height	13.5 in
Jaw Width	1.65 in
Length	15.75 in
Weight	15.2 lb
Width	3.5 in

## Electrical Ratings

Operating Voltage 18 VDC

## Conductor Related

Crimping Ranges  
Copper: #14 sol. - 750 kcmil;  
Aluminum: #8 sol. - 750 kcmil;  
ACSR: #4 AWG - 556.5 kcmil;  
Ground Rod: 1/2" - 1" diameter

## Certifications And Compliance

Standards - RoHS Compliance EX Status

## Logistics

Carton Quantity 1  
Minimum Pack Quantity 1  
Package Contents Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag  
Pallet Quantity 12

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50106125](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-PAT750CLIPB-SPEC-EN | REV 6/2024