



CSUDO252810250B, Cold Shrink Med Volt Termination Kit, 25-28kV Utility, Bare Concentric Neutral Outdoor Sleeve Only

By Burndy
Catalog # CSUDO252810250B

The Type CSUDO2528-B Series of Bare Concentric Neutral 25-28 kV Sleeve (Outdoor) Only cold shrink termination kits feature a geometric stress cone for exceptional performance. Kit includes outdoor cold shrink termination, center endseal termination, and installation guide. Conforms to IEEE-48-2009, Class 1 and ISO/IEC 17025 Standards. Test reports available upon request.

Features

- Rip and Grip Does not require heat gun or any installation tools
- Spiral rip cord design provides for easy installation with effortless unwinding providing for fast removal of the hold-out core, Rip cord is recyclable
- All kits supplied with indoor cold shrink termination, center endseal termination, and installation guide
- Quick, easy, cost effective installation utilizing one-piece terminator design
- Test reports available upon request
- L'agrippe-câble ne nécessite pas de pistolet thermique ni d'outils d'installation
- La conception en spirale de l'agrippe-câble permet une installation facile avec un déroulement sans effort permettant un retrait rapide du noyau de retenue, l'agrippe-câble est recyclable
- Toutes les trousse sont fournies avec une terminaison intérieure rétractable à froid, une terminaison centrale et un guide d'installation
- Installation rapide, facile et rentable grâce à la conception d'une terminaison monobloc
- Rapports d'essai disponibles sur demande

General

Boot Type	NO
Catalog Number	CSUDO252810250B
Environmental Conditions	
Material	Caoutchouc de silicone
Pin Type	N/A
Series	UD-BCN
Terminal Type	N/A
Type	
UPC	621945584860

Electrical Ratings

Phase	1-Phase
Voltage Rating	25/28 kV

Conductor Related

Conductor Range	1/0 AWG - 250 kcmil
-----------------	---------------------

Logistics

Carton Quantity	3
Pallet Quantity	84

Product Assets

- [Brochures - Cold Shrink Medium Voltage Cable Terminations Brochure](#)
- [Catalog Page - BURNDY MVColdShrinkTerminationKits CSUDO-B CSUDO-J CatCut](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50095766-01](#)
- [Specifications - CSUDO252810250B Specification Sheet French](#)





A Hubbell brand