

KS223, Split Bolt Connector, Run/Tap: #6 AWG Str-#2 AWG Sol

By Burndy
Catalog # [KS223](#)

Copper Split Bolt, Cu: 6 AWG (Str)-2 AWG (Sol) (Run & Tap).



General

Application	For Direct Burial Applications, Copper, Copperweld
Catalog Number	KS223
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	275 LBS/in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS-3, Compact
UPC	781810022504
UPC 12 Digit	7818100225044

Dimensions

Dimension - Cross Flats inch	.74 in
Dimension - L Length Overall mm	34 mm
Dimension - Length Overall inch	1.5
Dimension - Width inch	0.84 in
Dimension - Width mm	21 mm
Width	0.6 in

Conductor Related

Conductor - Copper Solid Run	2 AWG
Conductor - Copper Solid Run Range	2 AWG
Conductor - Copper Solid Tap	2 AWG
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Run Range	6 STR - 3 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	6 STR - 3 STR
Conductor - CopperWeld Solid Run	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - CopperWeld Solid Run Range	8 AWG-4 AWG
Conductor - CopperWeld Solid Tap	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - CopperWeld Solid Tap Range	8 AWG-4 AWG
Conductor - CopperWeld Str Run	6 D AWG;5 A AWG;5 D AWG;5 P AWG;4 A AWG
Conductor - CopperWeld Str Run Range	6 D AWG-4 A AWG
Conductor - CopperWeld Str Tap	6 D AWG;5 A AWG;5 D AWG;5 P AWG;4 A AWG
Conductor - CopperWeld Str Tap Range	6 D AWG-4 A AWG
Conductor Type	CU C Solid-Run
	CU C Str-Run
	CU Weld C Solid-Run
	CU Weld C Str-Run
	CU C Str-Tap
	CU Weld C Solid-Tap
	CU Weld C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Pallet Quantity	17400

Product Assets

[3D Models - KS223_MODEL-PDF](#)
[3D Models - KS223_MODEL-IGES](#)
[3D Models - KS223_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KS3_Lineart](#)
[Sales Drawings - SC..078560-01](#)
[Sell Sheets - SERVIT® Split-bolt Connectors](#)



A Hubbell brand