



# PENA13QT, Oxide Inhibitor, Quart Container

By Burndy  
Catalog # [PENA13QT](#)



Oxide Inhibiting Electrical Joint Compound, 1 Quart, For Al-Al, Al-Cu & Al Conduit Threads / Insulated Cable.

### Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

### Application

For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit

### General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA13QT
Container Type	Tub
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	A13
UPC	781810592922

UPC 14 Digit GTIN	00781810592922
Viscosity at 100 Fahrenheit	250 °F

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Container Size	1 Quart
----------------	---------

### Product Assets

- [3D Models - PENA13QT\\_MODEL-STEP](#)
- [3D Models - PENA13QT\\_MODEL-PDF](#)
- [3D Models - PENA13QT\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_PENA13QT\\_LineArt](#)
- [Sales Drawings - 50016095](#)
- [SDS - PENETROX A-13 FRENCH SDS](#)
- [SDS - PENETROX A-13 SDS](#)
- [SDS - PENETROX A-13 ESPANOL SDS](#)
- [SDS - SDS - Dutch - Penetrox A-13](#)
- [SDS - PENETROX A-13 GERMAN SDS](#)
- [SDS - PENETROX A-13 ITALIAN SDS](#)
- [SDS - PENETROX A-13 PORTUGUESE SDS](#)
- [Specifications - PENA13QT Specification Sheet English](#)
- [Specifications - PENA13QT Specification Sheet French](#)



A Hubbell brand