



# Compression Terminal

By Burndy  
Catalog # [YA3CLNT14](#)

3 AWG CU, One Hole, 1/4 Standard Barrel, Inspection Window, Narrow Tongue Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, WHITE Color Code, 9 Die Index.



## Application

Wire Termination

## General

Catalog Number	YA3CLNT14
Color Code	White
Connector Type	STANDARD BARREL
Die Index	9
Feature - Barrel Style	<ul style="list-style-type: none"><li>• Chamfered</li><li>• Skived</li></ul>
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810498163

## Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	0.70 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.82 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Z (inch)	0.39 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor - Copper Str Size	3 AWG
Conductor - Copper Str Size Range	3 AWG
Conductor - Material	COPPER
Conductor Size	3 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Pallet Quantity	76800

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)  
[Sales Drawings - 30003952](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YA3CLNT14-SPEC-EN | REV 6/2024