



# Compression H-Tap

By Burndy  
Catalog # YH298CWC

Copper Compression H Tap w/ Black Flame Retardant Cover, 250 kcmil-2 AWG (Main ), 8-14 AWG (Tap 1 & Tap 2), Tin Plated.



### Application

Wire Tap

### General

Catalog Number	YH298CWC
Color Code	Purple
Connector Type	H-TAP W/BLK COVER
Die Index	654
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810000304
UPC 12 Digit	7818100003044

### Dimensions

Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.90 in
Dimension - Strip Length inch	1-1/16
Dimension - Width inch	1.52 in

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Flex G Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex G Tap	14;8
Conductor - Copper Flex G Tap Range	8 AWG-14 AWG
Conductor - Copper Flex H Tap	14;8
Conductor - Copper Flex H Tap Range	8 AWG-14 AWG
Conductor - Copper Flex I Run	4/0 AWG-2 AWG
Conductor - Copper Flex I Tap	14;8
Conductor - Copper Flex I Tap Range	8 AWG-14 AWG
Conductor - Copper Flex K Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex K Tap	14;8
Conductor - Copper Flex K Tap Range	8 AWG
Conductor - Copper Flex M Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex M Tap	14;8
Conductor - Copper Str Run	2;1;1/0;2/0;3/0;4/0;250
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap	14;12;10;9;8
Conductor - Copper Str Tap Range	8 AWG-14 AWG
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	25
Pallet Quantity	2250

**Product Assets**

- Catalogs - Full Line BURNDY Catalog
- Catalogs - Section C - Compression Connections
- Customer Notices - Prop 65 Notice
- Sales Drawings - SD..206566-01



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YH298CWC-SPEC-EN | REV 6/2024