



YH3939WCC, Cu Compression H Tap and Clear Cover, 750-500 kcmil Run, 750-350 kcmil Tap

By Burndy
Catalog # [YH3939WCC](#)



Cu-code-H-Tap Crimpit, 750-500(550-500)(Main), 750-350(550-350), Flame retardent.

Application

Wire Tap

General

Catalog Number	YH3939WCC
Color Code	Yellow
Connector Type	H-TAP W/CLR COVER
Die Index	KR
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810436493
UPC 12 Digit	7818104364933

Dimensions

Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Strip Length inch	1-3/8
Dimension - Width inch	2.97 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	450;500
Conductor - Copper Flex G Tap	350;400;450;500
Conductor - Copper Flex H Tap	350;400;450;500
Conductor - Copper Flex I Run	550 KCMIL-450 KCMIL
Conductor - Copper Flex I Tap	350;400;450;500
Conductor - Copper Flex I Tap Range	550 KCMIL-350 KCMIL
Conductor - Copper Flex K Run	450;500
Conductor - Copper Flex K Tap	350;400;450;500
Conductor - Copper Flex M Run	450;500
Conductor - Copper Flex M Tap	350;400;450;500
Conductor - Copper Str Run	500;550;600;700;750
Conductor - Copper Str Run Range	750 KCMIL-500 KCMIL
Conductor - Copper Str Tap	350;400;450;500;550;600;700
Conductor - Copper Str Tap Range	750 KCMIL-350 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Pallet Quantity	450

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR YH2929WCC LineArt](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YH3939WCC-SPEC-EN | REV 6/2024