



# YAS28R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy  
Catalog # [YAS28R2N](#)



Aluminum Stacking Terminal - Straight lug, 4/0 AWG Al, Cu  
4/0 AWG ACSR, Pink.

## General

|  |               |
|--|---------------|
| Color Code                                     | Pink          |
| Connector Type                                 | Terminal      |
| Die Index                                      | 249;840;CSA24 |
| Feature - Barrel Style                         | Tapered       |
| Material                                       | Aluminum      |
| Physical Attribute - Number of Crimps Required | 1             |
| Physical Attribute - Number of Holes           | 2             |
| Plated   | N             |
| Plating Type                                   | Unplated      |
| Trade Name                                     | HYLUG™        |
| UPC  | 781810050422  |
| UPC 12 Digit                                   | 7818100504222 |

## Dimensions

|                                   |            |
|-----------------------------------|------------|
| Dimension - B Length inch         | 1.47 in    |
| Dimension - D inch                | 3.76 in    |
| Dimension - Hole Size inch        | 0.56 in    |
| Dimension - L Length Overall mm   | 148 mm     |
| Dimension - Length Overall inch   | 5.83 in    |
| Dimension - N inch                | 0.63 in    |
| Dimension - Outside Diameter inch | 0.91 in    |
| Dimension - Pad Width inch        | 1.24 in    |
| Dimension - Strip Length inch     | 1-19/32 in |
| Dimension - Z (inch)              | 1.38 in    |
| Physical Attribute - Tongue Angle | Straight   |

## Conductor Related

|                                   |                       |
|-----------------------------------|-----------------------|
| Conductor - ACSR Str Size         | 4/0 (6/1) Penquin AWG |
| Conductor - ACSR Str Size Range   | 4/0 (6/1) Penquin AWG |
| Conductor - AL Str Size           | 4/0 AWG               |
| Conductor - AL Str Size Range     | 4/0 AWG               |
| Conductor - Copper Str Size       | 4/0 AWG               |
| Conductor - Copper Str Size Range | 4/0 AWG               |

## Certifications And Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 20   |
| Pallet Quantity | 5920 |

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE208417](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YAS28R2N-SPEC-EN | REV 6/2024