

Compression Terminal

By Burndy
Catalog # [YAZ8C2TC38](#)

8 AWG CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Long Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Red Color Code, 49 Die Index.



Application

Wire Termination

General

Color Code	Red
Connector Type	LONG BARREL
Die Index	49
EU RoHS Indicator	Yes
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810227589
UPC 12 Digit	7818102275899

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.76 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	23 (7) Navy
Conductor - Copper Str Size	8 AWG
Conductor - Material	COPPER
Conductor Size	8 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	96000

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SE211915-04](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Z inch 0.43 in
Physical Attribute - Tongue Straight
Angle



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAZ8C2TC38-SPEC-EN | REV 6/2023