



YCB2R, Al Stirrup Connector, hot-line clamp adapter with Al run and Cu bail

By Burndy
Catalog # [YCB2R](#)



Permanent compression hot-line clamp adapter with aluminum run and copper bail. Permits hot-line tapping without arcing or chafing damage to aluminum conductor, Aluminum: 2 Str. - 6 Sol.

Application

For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors

General

Catalog Number	YCB2R
Die Index	BG
EU RoHS Indicator	Yes
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	CRIMPIT
Type	Stirrups
UPC	781810151501
UPC 12 Digit	7818101515011

Dimensions

Dimension - Bail Size	0.25 in
Dimension - D inch	2.50 in
Dimension - F Width Center to Center inch	2.50 in
Dimension - Height inch	3.75 in
Dimension - L Length Overall mm	227 mm
Dimension - Length Overall inch	8.95 in
Dimension - Width inch	0.72 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - ACSR Str Size	4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	4 AWG;2 AWG
Conductor - AL Str Size Range	4 AWG-2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[3D Models - YCB2R_MODEL-IGES](#)
[3D Models - YCB2R_MODEL-STEP](#)
[3D Models - YCB2R_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YCBR_Lineart](#)
[Sales Drawings - SD..029790-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YCB2R-SPEC-EN | REV 6/2024