




GAR3904TC, Mechanical Ground Connector, For 2 Hole Lug to Pipe or Rod

By Burndy
Catalog # [GAR3904TC](#)

Water Pipe Ground Connector, 2-1/2"- 3-1/2" Rod, Large, smooth connector contact area between pipe and ground clamp



Features

- Large, smooth connector contact area between pipe and ground clamp to maximize contact area between connector and pipe
- Pre-drilled pad for 2-3/8" bolts on 1" centers to allow for direct mounting of 2-hole compression terminals up to 750 kcmil to pipe
- One-wrench installation
- UL467 Listed for the US and Canadian Markets

Application

For Direct Burial, Water Pipe As Well As Structural And Reinforcing Rod Shapes

General

Catalog Number	GAR3904TC
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	3
Physical Attribute - Pad Configuration	2.50 x 2.50 - 3 Holes
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	Rod or Tube Clamp with Mounting Pad
U Bolt Type	1033
UPC	781810001578
UPC 12 Digit	7818100015788

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Height inch	6.50 in
Dimension - Length Overall inch	2.50 in
Dimension - Outside Diameter inch	4.00 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Width inch	6.50 in
Dimension - Width mm	165 mm

Conductor Related

Conductor - Copper Tube EH Size	2 1/2;3 1/2
Conductor - Copper Tube EH Size Range	2 1/2-3 1/2
Conductor - Pipe or Round Tube Size	2.5 - 3.5 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_GAR3900_Lineart](#)

[Sales Drawings - se..206158-01](#)

[Specifications - BURNDY_GAR3904TC_Specsheet](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-GAR3904TC-SPEC-EN | REV 8/2024