



YGA2C2N Compression Grounding Lug, #2 Str Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YGA2C2N](#)

HYLUG™ Copper Compression Terminal for Grounding; 2-Hole; 1/2" Stud; 1-3/4" Spacing; Long Barrel; Accommodates: #2 Str; 4.71" Length

Features

- Irreversible Compression Grounding Lug
- Inspection port to ensure proper cable insertion
- UL 467 Listed, acceptable for direct burial in earth or concrete
- Prefilled with PENETROX Oxide Inhibiting Compound and strip sealed
- 2 Stud Holes, 1/2" Holes, 1-3/4" Spacing
- Die Index: 10

Application

For Grounding Applications And Direct Burial In Earth Or Concrete

General

Catalog Number	YGA2C2N
Color Code	Brown
Connector Type	Terminal
Die Index	10
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminals
UPC	781810220306
UPC 14 Digit GTIN	00781810220306

Dimensions

Dimension - B Length fraction	1-2/9 in
Dimension - B Length inch	1.22 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	120 mm



Dimension - Length Overall inch	4.71 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Width fraction	2/5 in
Dimension - Width inch	0.41 in

Conductor Related

Conductor - Copper Str Size	2 Str.
Conductor - Copper Str Size Range	2 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Pallet Quantity	24000

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_YGA2N_LineArt

Sales Drawings - SD..082469-01
Specifications - YGA2C2N Specification Sheet French
Specifications - YGA2C2N Specification Sheet English



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY_CA-YGA2C2N-SPEC-EN | REV 4/2025