

# KLU25, Copper Terminal, Offset Tongue, 1 Hole, 14-10 AWG (Sol), #6 Stud, 1 Screw

By Burndy  
Catalog # [KLU25](#)



Copper Terminal, Offset Tongue, 1 Hole, 14-10 AWG (Sol), #6 Stud, 1 Screw.

## Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar And Offset Tongue, Non-Plated

## General

Catalog Number	KLU25
Connector Type	Pressure Bar
EU RoHS Indicator	Yes
Hardware Type	No. 8-32 Slotted RoundMachine Screw
Installation Torque Recommended in-lb	20
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810351369

## Dimensions

Dimension - B Length fraction	9/32 in
Dimension - B Length inch	0.28 in
Dimension - Bolt Size fraction	#6
Dimension - Height mm	0 mm
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4 mm
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - N inch	0.21 in
Dimension - Pad Width inch	0.31 in
Dimension - Screw Size inch	8-32

Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	#6

## Conductor Related

Conductor - Copper Solid Size Range	14;13;12;11;10
Conductor - Copper Solid Size	14-10
Conductor - Copper Str Size Range	14;12;10
Conductor - Copper Str Size	14-10
Conductor Size	14-10 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	600
-----------------	-----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_KLU\\_LineArt](#)
- [Sales Drawings - sd207469-01](#)
- [Specifications - KLU25](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_MX-KLU25-SPEC-EN | REV 10/2024