


# T10516, Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # T10516



Uninsulated Ring Terminal For 12 - 10 AWG.

## Features

Long neck terminal permits easy bending and stacking of several terminals on a common stud

## Application

For Control Wiring And Other Standard Duty Applications

## General

Catalog Number	T10516
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810722350
UPC 12 Digit	7818107223500

## Dimensions

Cable Insulation Diameter Maximum	0.12 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Bolt Size fraction	5/16
Dimension - Diameter Max Size inch	0.12 in
Dimension - Hole Size fraction	1/3
Dimension - Hole Size inch	0.33 in
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.53 in

Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	5/16
Dimension - Z (inch)	0.41 in

## Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	600
Pallet Quantity	99999

## Product Assets

- [3D Models - T10516\\_MODEL-PDF](#)
- [3D Models - T10516\\_MODEL-IGES](#)
- [3D Models - T10516\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_K6FT\\_LineArt](#)
- [Sales Drawings - 50094154](#)
- [Specifications - T10516](#)



A Hubbell brand