

C11K16D, Cast Bronze Ground Clamp for Water Pipe, Rebar, Ground Rod, to Tap Conductor

By Burndy
Catalog # C11K16D



Cast Bronze Ground Clamps, Water Pipe-1/2" - 1" (13 -25) (Run), Rebar-#4 -#6 (Run), Ground Rod -3/8"-1" (Run), Ground-#10-#2 Str. (Tap).

Features

- Lay-In Feature
- Connects Grounding Conductor to Water Pipe, Copper Tube, Ground Rod or Rebar
- Open face design allows for a fast lay-in on the tap conductor without need for cutting
- Reverse bottom clamp for smaller size, rebar or rod

Application

For Connecting Grounding Conductor To Water Pipe, Copper Tube, Ground Rod Or Rebar, Direct Burial Applications

General

Catalog Number	C11K16D
EU RoHS Indicator	Yes
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810358641
UPC 12 Digit	7818103586411

Dimensions

Dimension - Height inch	1.64 in
Dimension - Height mm	41.7 mm
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.28 in
Dimension - Width inch	0.66 in
Dimension - Width mm	17 mm

Conductor Related

Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3
-----------------------------	--

Conductor - Copper Str Size Range	AWG;2 AWG 10 AWG-2 AWG
Conductor - Pipe EMT Size Range	1/2 in;3/4 in;1 in 1/2 in-1 in
Conductor - Rebar Size Range	4 ;5 ;6 4 -6
Conductor - Rod Size Range	3/8 in;1/2 in;5/8 in;3/4 in;7/8 in;1 in 3/8 in-1 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

- [3D Models - C11K16D_MODEL-STEP](#)
- [3D Models - C11K16D_MODEL-PDF](#)
- [3D Models - C11K16D_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_C11K16D_LineArt](#)
- [Sales Drawings - 10037615](#)
- [Specifications - C11K16D](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-C11K16D-SPEC-EN | REV 10/2024