



KK4A36U4N, AL Universal Terminal, 4 Conductor, 2 AWG Str-600 kcmil, 4-Hole, 1/2" Stud, 1.75" Spacing, 8 Screws, Al/Cu Rated

By Burndy

Catalog # [KK4A36U4N](#)

Aluminum Universal Terminal, 4 Conductor, 4 Hole, 2 AWG (Str)-600 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 8 Screws, Al/Cu Rated, Tin Plated.

Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

Application


For Aluminum and Copper Conductors

General

Catalog Number	KK4A36U4N
Connector Type	Parallel Set-Screw
EU RoHS Indicator	Yes
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL TERMINAL
Type	Bolted Lugs & Terminals
UPC	781810601112

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	1.51 in
Dimension - Height mm	38.4 mm
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.63 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	5.04 in



Dimension - Stud Size inch 0.56 in

Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Size Range	2 Str. - 600 Kcmil
Conductor - Copper Str Size Range	2 Str. - 600 Kcmil
Conductor Size	2 AWG-600 KCMIL
Conductor Type	- CU C Str-Size - AL C Str-Size
Number Of Wires	4
Number of Conductors	4

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Product Assets

[3D Models - KK4A36U4N_MODEL-IGES](#)
[3D Models - KK4A36U4N_MODEL-PDF](#)
[3D Models - KK4A36U4N_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KK4A-U_LineArt](#)



A Hubbell brand