

KLU70, Mechanical Offset Tongue, #8 Sol-#2 AWG Str, 1-Hole, 1/4" Stud, 1 Screw

By Burndy
Catalog # KLU70



Copper Terminal, Offset Tongue, 1 Hole, 8 AWG (Sol)-2 AWG (Str), 1/4" Stud, 1 Screw.

Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar

General

Catalog Number	KLU70
Connector Type	Pressure Bar
EU RoHS Indicator	Yes
Hardware Type	5/16 UNF Slotted SetScrew
Installation Torque	40
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810351383

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Size fraction	1/4
Dimension - Height mm	0 mm
Dimension - Hole Size inch	0.26 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	39 mm

Dimension - Length Overall inch	1.55 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.47 in
Dimension - Screw Size inch	5/16
Dimension - Strip Length inch	3/4
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor Size	8-2 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	600
-----------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

