



Compression Terminal

By Burndy
Catalog # [YA322TC38](#)

400 kcmil CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Blue Color Code, 19 Die Index.



Application

Wire Termination

General

Catalog Number	YA322TC38
Color Code	Blue
Connector Type	LONG BARREL
Die Index	19
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810019948
UPC 12 Digit	7818100199488

Dimensions

Dimension - B Length fraction	2-1/8 in
Dimension - B Length inch	2.12 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	118 mm
Dimension - Length Overall inch	4.66 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	2-3/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	400 (127) Navy
Conductor - Copper Str Size	400 KCMIL
Conductor - Copper Str Size Range	400 kcmil
Conductor - Material	COPPER
Conductor Size	400 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SE..208777-01](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YA322TC38-SPEC-EN | REV 6/2024