



**YGA292N Compression Grounding  
Lug, 250 kcmil Cu, 2-Hole, 1/2"  
Stud, 1-3/4" Spacing**

By Burndy  
Catalog # [YGA292N](#)

HYLUG™ Copper Compression Terminal for Grounding; 2-Hole;  
1/2" Stud; 1-3/4" Spacing; Long Barrel; Accommodates: 250  
kcmil; 5.16" Length



## Application

For Grounding Applications And Direct Burial In Earth Or Concrete

## General

Catalog Number	YGA292N
Color Code	Yellow
Connector Type	Terminal
Die Index	16
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminals
UPC	781810220337
UPC 12 Digit	7818102203377

## Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.21 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.09 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Width fraction	1/2 in
Dimension - Width inch	0.53 in

## Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>• UL 467,486A</li><li>• CSA Certified</li><li>• Direct Burial</li></ul>
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Pallet Quantity	4640

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YGA2N\\_LineArt](#)  
[Sales Drawings - SD..082469-01](#)  
[Specifications - YGA292N](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_MX-YGA292N-SPEC-EN | REV 8/2024