

YGHP2C2 Figure 6 Compression Grounding Connector, #6 Sol-#2 Str Run and Tap

By Burndy
Catalog # [YGHP2C2](#)



Cu Compression Ground Tap Connector, #6 Sol- #2 Str(Run & Tap).

Features

- Irreversible compression ground tap can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth And Concrete

General

Catalog Number	YGHP2C2
Connector Type	Tap
Die Index	O
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of	1
Crimps Required	
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810220917
UPC 12 Digit	7818102209177

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Height mm	0 mm

Conductor Related

Conductor - Copper Solid Run	6
Conductor - Copper Solid Run Range	6
Conductor - Copper Solid Tap	6

Conductor - Copper Solid Tap Range	6
Conductor - Copper Str Run	6;5;4;3;2
Conductor - Copper Str Run Range	6-2
Conductor - Copper Str Tap	6;5;4;3;2
Conductor - Copper Str Tap Range	6-2

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837 • IEEE 837 2014 Qualified
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Pallet Quantity	17400

Product Assets

[3D Models - YGHP2C2_MODEL-IGES](#)
[3D Models - YGHP2C2_MODEL-STEP](#)
[3D Models - YGHP2C2_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YGHPC_Lineart](#)
[Sales Drawings - sd082473-01](#)
[Specifications - YGHP2C2](#)



A Hubbell brand