



Compression Splice Reducer

By Burndy
Catalog # [YSR3126FXLTCKITC](#)

CU Splice Reducer, Barrel A 350 kcmil, Barrel B 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Red/Black Color Code, 18/13 Die Index.



Application

Wire Reducing Splice

General

Catalog Number	YSR3126FXLTCKITC
Color Code	Red, Pink
Color Code - Side A	Red
Color Code - Side B	Black
Connector Type	STANDARD BARREL KITS
Die Index	18/13
Die Index - Element A	18
Die Index - Element B	13
Die Index Run Side	18
Die Index Tap Side	13
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
UPC	781810458839
UPC 12 Digit	7818104588399

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.49 in
Dimension - L Length Overall mm	82 mm
Dimension - Length BB inch	1.16 in
Dimension - Length Overall inch	3.24 in
Dimension - Strip Length inch	1.41 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Size B	1/0 AWG
Conductor - Copper Flex G Tap	2/0 AWG
Conductor - Copper Flex H Size B	1/0 AWG
Conductor - Copper Flex H Tap	2/0 AWG
Conductor - Copper Flex I Size B	1/0 AWG
Conductor - Copper Flex I Tap	2/0 AWG
Conductor - Copper Flex K Size B	1/0 AWG
Conductor - Copper Flex K Tap	2/0 AWG
Conductor - Copper Flex M Size B	1/0 AWG
Conductor - Copper Flex M Tap	2/0 AWG
Conductor - Copper Str Size	350 KCMIL-2/0 AWG
Conductor - Copper Str Size A	350 kcmil
Conductor - Material	COPPER
Conductor Size	350 KCMIL-2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	350 KCMIL-2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Pallet Quantity	1728

Product Assets

- [3D Models - YSR3126FXLTCKITC_MODEL-IGES](#)
- [3D Models - YSR3126FXLTCKITC_MODEL-PDF](#)
- [3D Models - YSR3126FXLTCKITC_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YSR3126FXLTCKITC-SPEC-EN | REV 6/2024