




Straight Blade Devices, Receptacles, Hospital Grade QUADPLEX Receptacle, Surge Suppression, Isolated Ground, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R

By Bryant
Catalog # 21254HSIA



Straight Blade Devices, Receptacles, Hospital Grade
QUADPLEX Receptacle, Surge Suppression, Isolated Ground,
20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

Application

Quad-Plex

General

Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Visual Status Indicator
Item Type	Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Outlets	4
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Hospital Grade
Type	Four Outlet Receptacle
UPC	781786190290

Dimensions

Dimensions	4.3 in x 4.30 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	4.3 in
Weight	0.35 lb
Width	4.30 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant D-3 Catalog page](#)
[Catalog Page - Bryant B-5 Catalog page](#)
[Catalog Page - Bryant A-6 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Healthcare Solutions](#)
[Literature - General Literature - Surge Protection Devices](#)

Related Products

[21254HSA - Straight Blade Devices, Receptacles, Hospital Grade QUADPLEX Receptacle, Surge Suppression, Isolated Ground, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R](#)

[4SQBXI - Straight Blade Devices, Accessories, 4" Square Portable Box with Cord Grip, Quad Plex Receptacles, Ivory, Single Pack](#)

[21254HIGO - Straight Blade Devices, Receptacles, Quad-PLEX, Hospital Grade, Isolated Ground, 20A 125V, 2 -Pole 3-Wire Grounding, 5-20R, Orange, Single Pack](#)

[ADAPI - Straight Blade Devices, Accessories, 1 and 2 Gang Adapter Plate, Quad-Plex Receptacles, Ivory, Single Pack](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-21254HSIA-SPEC-EN | REV 5/2023