



Locking Devices, Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Wye 120/208V AC, Non-NEMA

By Bryant
Catalog # 3523

Locking Devices, Industrial, Female Connector Body, 20A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Black and White.



Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Heavy Duty Industrial

General

| | |
|------------------------------|---|
| Color | Black, White |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Insulation | Insulated Body |
| Item Type | 20A Nylon Connector Non-NEMA |
| Material | Composite |
| Material - Mounting Hardware | Cord Mounted |
| Number Of Poles | 4-Pole |
| OEM Brand Name | Hubbell Bryant |
| Style | Internal Cord Clamp |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |
| Type | Connector Body |
| UPC | 781786651708 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 2.11 in x 2.11 in x 3.73 in |
| Display Size | Standard Sized Product |
| Height | 3.73 in |
| Length | 2.11 in |
| Width | 2.11 in |

Electrical Ratings

| | |
|----------------------------|-----------------------|
| Amperage Rating | 20 A |
| Connectivity | Screw Terminals |
| Current Rating | 20 A |
| Voltage Rating | 3 Phase Y 120/208 VAC |
| Voltage Rating Description | 3 Phase Y 120/208 VAC |

Conductor Related

| | |
|----------------------|----------------------|
| Conductor Range | #12 AWG to #8 AWG |
| Number Of Conductors | 3-Wire Non-Grounding |
| Number Of Wires | 5-Wire |
| Wire Size | #18 AWG to #8 AWG |

Certifications and Compliance

| | |
|-------------|----------|
| Nema Rating | Non-NEMA |
|-------------|----------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Bryant H-16 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[70204ANA - Locking Devices, Accessories, Angle Adapter for Plugs and Connectors, For 20A and 30A Black and White](#)
[72002BCB - Locking Devices, Accessories, Long Weatherproofing Boot, For 20A and 30A, Black](#)
[3521 - Locking Devices, Locking Devices, Industrial, Male Plug, 20A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Non- NEMA, Screw Terminal and White](#)
[72002BC - Locking Devices, Accessories, Long Weatherproofing Boot, For 20A and 30A, Yellow](#)



A proud member of the Hubbell Family.

