

YAEV14T2, Nylon Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAEV14T2](#)



Ring Tongue Terminal, Straight, 600 V, 0.38 in W, Nylon insulation, Tin Plated, 20-14 AWG, 1/4 in stud size

Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

General

Catalog Number	YAEV14T2
Color Code	Blue
Connector Type	Ring Terminal
Construction Material - Main	Copper
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
Type	YAEV
UPC	781810082218
UPC 12 Digit	7818100822188

Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - N inch	0.26 in
Dimension - Pad Width inch	0.38 in
Dimension - Stud Size inch	1/4
Dimension - Width inch	0.10 in

Dimension - Z (inch) 0.32 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Str Aircraft Size	AN 18;AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 18-AN 14
Conductor - Copper Str Size	20AWG ,18 AWG, 16 AWG, 14 AWG
Conductor - Copper Str Size Range	20-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[3D Models - YAEV14T2_MODEL-STEP](#)
[3D Models - YAEV14T2_MODEL-IGES](#)
[3D Models - YAEV14T2_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094163](#)



A Hubbell brand