


YAEV8CH1, Nylon Ring Terminal For 8 AWG

By Burndy
Catalog # YAEV8CH1



Ring-Tongue Terminals, 8 Max. Insul.Dia.: .30" Sleeve, Color: Red, 6-8, 1.54 in L, Nylon-Insulated For Expanded Insulation, 600 Volts Max.

Application

For Very Demanding High Vibration Applications Encountered In Aircraft And Aboard Ships As Well As Motor Lead Applications In Hospitals, Industrials And Generating Plants

General

Catalog Number	YAEV8CH1
Color Code	Red
Connector Type	Ring Terminal
Die Index	435
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, INSULUG
Trade Name	INSULUG™
Type	YAEV-H
UPC	781810039595
UPC 12 Digit	7818100395955

Dimensions

Dimension - B Length fraction	3/8 in
Dimension - B Length inch	0.37 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.55 in
Dimension - Length Overall inch	1.60 in
Dimension - N inch	0.23 in
Dimension - Pad Width inch	0.46 in
Dimension - Strip Length inch	7/16

Dimension - Stud Size inch	1/4
Dimension - Z (inch)	0.28 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Aircraft Size Range	AN 8
Conductor - Copper Str Size	8
Conductor - Copper Str Size Range	8
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAEV6CH_LineArt](#)
[Sales Drawings - 50094164](#)
[Specifications - YAEV8CH1](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-YAEV8CH1-SPEC-EN | REV 10/2024