

YSU2R2W, Heavy-Walled Aluminum Tube with Solid Barrier

By Burndy
Catalog # YSU2R2W



Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code:Red (Side A), Orange (Side B).

Features

- Heavy-Walled aluminum tubing with solid barrier minimizes galvanic corrosion of conductors
- Accommodates neutral strands of Type SE Service Entrance Conductor as well as other conductors

Application

For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 and Compressed Conductors

General

Catalog Number	YSU2R2W
Color Code - Side A	Red
Color Code - Side B	Orange
Die Index	243;BG or 5/8
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Sub Brand	LINKIT
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated, Center Stop
UPC	781810141236
UPC 12 Digit	7818101412366

Dimensions

Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - ACSR Str Size A	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size A Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG

Conductor - ACSR Str Size B	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size A	2 AWG;1 AWG
Conductor - AL Str Size A Range	2 AWG-1 AWG
Conductor - AL Str Size B	3 AWG, 4 AWG
Conductor - AL Str Size B Range	3 AWG- 4 AWG
Conductor - Copper Solid Size B	2 AWG
Conductor - Copper Str Size A	1 AWG, 2 AWG, 3 Awg
Conductor - Copper Str Size A Range	1 AWG-3 AWG
Conductor - Copper Str Size B	3 AWG, 4 AWG
Conductor - Copper Str Size B Range	3 AWG- 4 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
Pallet Quantity	29600

Product Assets

- [3D Models - YSU2R2W_MODEL-PDF](#)
- [3D Models - YSU2R2W_MODEL-IGES](#)
- [3D Models - YSU2R2W_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YSU_LineArt](#)
- [Sales Drawings - sd052025-04](#)



A Hubbell brand