

YSU2W2W, Heavy-Walled Aluminum Tube with Solid Barrier

By Burndy
Catalog # YSU2W2W



Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code:Orange (Side A), Orange (Color Code).

Features

- Heavy-walled aluminum tube with solid barrier minimizes galvanic corrosion of conductors
- Accommodates neutral strands of SE Service Entrance Conductors as well as others
- Installed with standard tooling, color-coded, and pre-filled with PENETROX Joint Compound and Stripsealed

Application

For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 and Compressed Conductors

General

Catalog Number	YSU2W2W
Color Code - Side A	Orange
Color Code - Side B	Orange
Die Index	243;BG or 5/8
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Sub Brand	LINKIT
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated, Center Stop
UPC	781810141946
UPC 12 Digit	7818101419466

Dimensions

Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - ACSR Str Size A	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
-----------------------------	--------------------------------------

Conductor - ACSR Str Size A Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size A Range	3 AWG, 4 AWG
Conductor - AL Str Size A Range	3 AWG- 4 AWG
Conductor - AL Str Size B Range	3 AWG, 4 AWG
Conductor - AL Str Size B Range	3 AWG- 4 AWG
Conductor - Copper Solid Size A	2 AWG
Conductor - Copper Solid Size B	2 AWG
Conductor - Copper Str Size A Range	3 AWG, 4 AWG
Conductor - Copper Str Size A Range	3 AWG-4 AWG
Conductor - Copper Str Size B Range	3 AWG, 4 AWG
Conductor - Copper Str Size B Range	3 AWG-4 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Pallet Quantity	29600

Product Assets

- [3D Models - YSU2W2W_MODEL-PDF](#)
- [3D Models - YSU2W2W_MODEL-IGES](#)
- [3D Models - YSU2W2W_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)



A Hubbell brand