

# YSV6CL, Uninsulated Splice For 6 AWG

By Burndy  
Catalog # YSV6CL



HYLINK™ Uninsulated Compression Butt Splice; Seamless Standard Barrel; Accommodates: #6 AWG Str/Sol, AN, Aircraft; Length: 1.12" ; 600 V Max; Bulk Package

## Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

## Application

For Aircraft, Light Duty Industrial And General Purpose Applications

## General

Catalog Number	YSV6CL
Connector Type	Seamless Butt Splice
Die Index	39
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810543856

## Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.12 in

Dimension - Outside Diameter inch	0.31 in
Dimension - Strip Length inch	5/8 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Size	6 AWG
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> <li>• CU C Str Aircraft-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	200
Pallet Quantity	99999

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YSV-L\\_LineArt](#)
- [Sales Drawings - 50094198](#)
- [Specifications - YSV6CL](#)