



# Locking Devices, Bryant Power Interrupting, Industrial, Female, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow

By Bryant  
Catalog # 26418



Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow polycarbonate outer cover and adjustable cord grip

## Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with stainless steel screws provide maximum termination strength and dependability
- Insulated, color coded metallic housing enhances safety and abuse resistance

## Application

Heavy Duty Industrial

## General

Color	Yellow
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	60A Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786584181

## Dimensions

Dimensions	3.18 in x 3.18 in x 6.52 in
Display Size	Standard Sized Product
Height	6.52 in
Length	3.18 in
Width	3.18 in

## Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current Rating	60 A
Voltage Rating	600 VAC
Voltage Rating Description	600 VAC

## Conductor Related

Conductor Range	#6 AWG to #4 AWG
Number Of Conductors	4-Wire Grounding
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalog Page - Bryant H-26 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[26422 - Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow](#)

[26419 - Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-26418-SPEC-EN | REV 5/2023

